

ULT 200.1



LASER FUMES



DUST AND SMOKE



SOLDERING FUMES



ODORS, GASES, AND VAPORS



CLEANING INDUSTRIAL GASES



NEW EMISSIONS



WELDING FUMES



OIL AND EMULSION MISTS



COMPLETE SOLUTIONS

Version: 09

Dated: 06/2019



Extraction. Filtration. Persistence.



Accessory articles

Devices.....	3
DN50 extraction system.....	4
DN80 extraction system.....	5
DN100 exhaust air extraction system	6
Interface accessories.....	6
Replacement filter.....	7

In conjunction with their filters, the ULT 200.1 filter devices offer a specific solution for all extraction purposes

ULT AG offers a range of selected suction hoses and accessories for individually configuring the ULT 200.1. The 90° bends and sleeves allow space-saving, permanent installation. The product range includes DN50 and DN80 diameters. For example, the Y-piece allows two extraction arms to be operated from a single DN50 connection on the device. The DN80 to DN75 reducer allows connection to System 75 extraction arms.

The ULT 200.1 can be operated with up to 4 extraction arms from the Danish manufacturer Alsident®. The practical mounting console allows an extraction arm to be mounted directly on the device. A wide range of System 50 and System 75 extraction are available for the device.

To ensure full capture, you can select collecting elements matching the pollution source. Extractor tubes offer full extraction performance in the smallest possible space, flat hoods concentrate the extraction flow, round hoods catch rising vapors and suction gaps allow extraction along a linear path.

The range of DN 100 hoses and sockets allow you to integrate the ULT 200.1 into your exhaust air extraction system.

For ergonomic integration of the ULT 200.1 into your workplace, ULT AG also offer a foot switch for switching the device on and off. The 8-pin M12- connection cable allows integration of the ULT 200.1 into your machine.

For worldwide operation, ULT provides country-specific power cables free of charge: in addition to the standard European CEE 7/7 cable, these also include Swiss, UK and US cables as desired.



Devices

The accessory portfolio relates to the following devices:

ACD – Odor, Gas and Vapors



ACD 200.1 MD.20 A6 50% Chemisorption 100% Chemisorption	230 m ³ /h - VFS	ACD 0200.1-MD.20.50.1001 ULT 0200.1-Opt.10 ULT 0200.1-Opt.11
ACD 200.1 MD.20 A14 50% Chemisorption 100% Chemisorption	230 m ³ /h - VFS	ACD 0200.1-MD.20.50.1006 ULT 0200.1-Opt.12 ULT 0200.1-Opt.13

ASD – Dust and Smoke



ASD 200.1 MD.20 H	230 m ³ /h-VFS	ASD 0200.1-MD.20.50.3059
ASD 200.1 MD.20 TH	230 m ³ /h-VFS	ASD 0200.1-MD.20.50.3060

LAS – Laser Fumes



LAS 200.1 MD.20 K	230 m ³ /h-VFS	LAS 0200.1-MD.20.50.6028
LAS 200.1 MD.20 TK	230 m ³ /h-VFS	LAS 0200.1-MD.20.50.6030

LRA – Soldering Smoke



LRA 200.1 MD.20 K	230 m ³ /h - VFS	LRA 0200.1-MD.20.50.6006
-------------------	-----------------------------	--------------------------

DN50 extraction system

Hoses



Flexible extraction hose DN 50, 2m	Antistatic, incl. 90° bend, socket and worm drive hose clips	ULT 06.1.300
Flexible extraction hose DN 50, 3m	Antistatic, incl. 90° bend, socket and worm drive hose clips	ULT 06.1.301
Flexible extraction hose DN 50, 5m	Antistatic, incl. 90° bend. socket and worm drive hose clips	ULT 06.1.302
Flexible extraction hose DN 50, per meter	Antistatic, without accessories	ULT 06.1.303

Hose accessories



Bend 90° DN 50	Antistatic, incl. worm drive hose clip	ULT 06.1.312
Socket DN 50	Antistatic, incl. worm drive hose clip	ULT 06.1.313
Y-piece DN 50 - 2*DN 50	Antistatic	ULT 06.1.316

Extraction arm mounting elements



ULT 200.1 S50 console	Series 200.1 For Alsident System 50	ULT 0200.1- Console.S50.01
Table bracket black	Alsident System 50, accessory	2-5010-050

Extraction arms



Alsident system 50, antistatic extraction arm	945 mm for table/device mounting	50-4737-1-6
---	----------------------------------	-------------

Collecting elements



Flat screen antistatic	Alsident System 50, accessory	1-503324-6
Round hood aluminium antistatic	Alsident System 50, accessory	1-5024-6
Extractor tube antistatic	Alsident System 50, accessory	1-5021-6
Suction gap antistatic	Alsident System 50, accessory	1-5020-6

DN80 extraction system

Hoses



Flexible extraction hose DN 80, 2m	Antistatic, incl. 90° bend, socket and worm drive hose clips	ULT 06.1.304
Flexible extraction hose DN 80, 3m	Antistatic, incl. 90° bend, socket and worm drive hose clips	ULT 06.1.305
Flexible extraction hose DN 80, 5m	Antistatic, incl. 90° bend, socket and worm drive hose clips	ULT 06.1.306
Flexible extraction hose DN 80, per meter	Antistatic, without accessories	ULT 06.1.307

Hose accessories



Bend 90° DN 50	Antistatic, incl. worm drive hose clip	ULT 06.1.314
Socket DN 50	Antistatic, incl. worm drive hose clip	ULT 06.1.315
Reducer DN 80 - DN 75	Antistatic, for connecting a DN80 hose to the System 75 extraction arm, incl. worm drive hose clip	ULT 06.1.317

Extraction arm mounting elements



ULT 200.1 S75 Console	Series 200.1 For Alsident System 75	ULT 0200.1- Console.S75.01
Table bracket white	Alsident System 75, accessory	2-7510

Extraction arms



Alsident System 75, Absaugarm	1290mm for table/device mounting	75-6555-1-5
-------------------------------	----------------------------------	-------------

Collecting elements



Flat screen	Alsident System 75, accessory	1-753324-5
Round hood aluminium	Alsident System 75, accessory	1-7524-5
Extractor tube	Alsident System 75, accessory	1-7525

DN100 exhaust air extraction system

Hoses and hose accessories



Flexible extraction hose DN 80, per meter	Antistatic, without accessories	ULT 06.1.311
Socket DN 100	Antistatic, incl. worm drive hose clip	ULT 06.1.318

Interface accessories

M12 interface accessories



M12 connection cable	incl. M12 Male adapter, length 3m	ULT 03.1.300
M12 On/Off foot switch	incl. M12 Male adapter, length 3m	ULT 03.1.301


Device power cables – supplied free of charge with ordered device



Swiss device power cable	Length 3.00 m	ULT 03.0.135
UK device power cable	Length 2.00 m	ULT 03.0.136
USA device power cable	Length 2.00 m	ULT 03.0.134
EU device power cable (CEE 7/7) - included as standard	Length 3.00 m	ULT 03.0.100


Replacement filter

ACD




Filter A6

G4 Z-Line filter	ULT 02.0.570
Adsorption filter cassette A6	ULT 02.1.501




Filter A14

G4 Z-Line filter	ULT 02.0.570
Adsorption filter cassette A14	ULT 02.1.504




Filter AC7

G4 Z-Line filter	ULT 02.0.570
Chemisorption filter cassette AC7	ULT 02.1.509




Filter AC17

G4 Z-Line filter	ULT 02.0.570
Chemisorption filter cassette AC17	ULT 02.1.847



Filter C11

G4 Z-Line filter	ULT 02.0.570
Chemisorption filter cassette C11	ULT 02.1.803




Filter C20

G4 Z-Line filter	ULT 02.0.570
Chemisorption filter cassette C20	ULT 02.1.827


Replacement filter

ASD



Filter H


Panel filter F - set of 5 pcs	ULT 02.0.592
Particle filter cassette H14	ULT 02.1.519



Filter TH


Pocket filter F - set of 5 pcs	ULT 02.1.557
Empty frame for pocket filter	ULT 02.1.528
Particle filter cassette H14	ULT 02.1.519

LAS



Filter K


Expanded metal filter	ULT 02.0.576
Prefilter set LAS K - set of 5 pcs	ULT 02.0.217
Combined filter cassette H14A	ULT 02.1.522



Filter TK

Expanded metal filter	ULT 02.0.576
Pocket filter F - set of 5 pcs	ULT 02.1.557
Empty frame for pocket filter	ULT 02.1.528
Combined filter cassette H14A + mat	ULT 02.1.529

LRA



Filter K

Expanded metal filter	ULT 02.0.576
Filter mat M5-02/F7-02 - set of 10	ULT 02.0.575
H13A combined filter cassette	ULT 02.1.521